

QT-Brightek PLCC2 Series PLCC2 Reverse Mount Red LED

Part No.: QBLP670R-R

Product: QBLP670R-R	Date: May 02, 2018	Page 1 of 9
	Version# 1.1	






Table of Contents:	
Introduction	3
Electrical / Optical Characteristic (T=25 °C)	4
Absolute Maximum Rating	4
Characteristic Curves (Ta=25°C)	5
Solder Profile & Footprint	
Packing	
Labeling	
Ordering Information	
Disclaimer	
	• • • • • • • • • • • • • • • • • • • •



Introduction

Feature:

- Clear lens
- Package in tape and reel
- Ultra bright reflector type PLCC2 LED
- AlInGaP technology for Red
- 120 degree viewing angle
- Reverse Mountable

Description:

These ultra bright reflector type PLCC2 LEDs have a height profile of 1.85mm. With a combination of high brightness output and robust package, these LEDs are ideal for architecture lighting, status indication, and industrial equipment lighting applications.

Application:


- Status indication
- Industrial equipment backlighting
- Architecture lighting

Certification & Compliance:

- TS16949
- ISO9001
- RoHS Compliant



Dimension:



Units: mm / tolerance = +/-0.2mm

Product: QBLP670R-R	Date: May 02, 2018	Page 3 of 9
	Version# 1.1	



Electrical / Optical Characteristic (T=25 °C)

Product	Color	I (m A)	V _F	(V)		λ _D (nm)		I _V (mo	cd)
Product	Color	I _F (mA)	Тур.	Max.	Min.	Min. Typ. Max		Min.	Тур.
QBLP670R-R	Red	20	2.0	2.4	615	623	630	490	760

Absolute Maximum Rating

Material	P _d (mW)	I _F (mA)	I _{FP} (mA)*	V _R (V)	T _{OP} (°C)	T _{ST} (°C)	T _{SOL} (°C)**
AllnGaP	72	30	125	5	-40 ~ +85	-40 ~ +100	260

^{*}Duty 1/10 @ 1KHz

Forward Voltage V_F @ I_F=20mA

_				
	Bin	Min.	Max.	Unit
	V1B	1.5	1.8	
Ī	V1C	1.8	2.1	V
Ī	V2A	2.1	2.4	

Luminous Intensity I_V @ I_F=20mA

	<i>J</i> • • •		
Bin	Min.	Max.	Unit
25	490	640	
26	640	830	mcd
27	830	1080	

Dominant Wavelength λ_D for Red @ I_F=20mA

Bin	Min.	Max.	Unit
A5	615	620	
R1	620	625	nm
R2	625	630	

Note:

Tolerance of measurement of forward voltage: ±0.1V Tolerance of measurement of luminous intensity: ±15% Tolerance of measurement of dominant wavelength: ±2nm

Product: QBLP670R-R	Date: May 02, 2018	Page 4 of 9
	Version# 1.1	

^{**}IR Reflow for no more than 10 sec @ 260 °C



Characteristic Curves (Ta=25°C)




Figure 1. Forward Current VS. Forward Voltage




Figure 2. Spectral Power Distribution vs. Wavelength




Figure 3. Forward Current vs. Ambient Temperature





Figure 4. Relative Luminosity VS. Radiation Angle


Product: QBLP670R-R	Date: May 02, 2018	Page 5 of 9
	Version# 1.1	



Solder Profile & Footprint

-The recommended reflow soldering profile is as follows (temperatures indicated are as measured on the surface of the LED resin):






Product: QBLP670R-R	Date: May 02, 2018	Page 6 of 9
	Version# 1.1	




Packing

Reel Dimension:



Unit: mm


Tape Dimension:



Symbol	A0	В0	KO	P0	P1	P2	Т
Spec	3.07±0.1	5.80±0.1	2.42±0.1	4.0±0.1	4.0±0.1	2.00±0.1	0.25±0.05
Symbol	E	F	D0	D1	w	10P0	
Spec	1.75±0.10	5.5±0.05	1.55±0.1	1.50±0.1	12±0.1	40.0±0.2	

Unit: mm

Packaging Specifications:



Product: QBLP670R-R	Date: May 02, 2018	Page 7 of 9
	Version# 1.1	



Labeling

Part No:
Customer P/N:
<u>ltem:</u>
Q'ty:
Vf:
Iv:
WI:
Date:

Ordering Information

Part #	Orderable Part #	Spec Range	Quantity per reel
QBLP670R-R	QBLP670R-R	Iv=490mcd min. @ 20mA, λd=615 to 630nm	2,000 units

Product: QBLP670R-R	Date: May 02, 2018	Page 8 of 9
	Version# 1.1	



Revision History

Description:	Revision #	Revision Date
New Release of QBLP670R-R	V1.0	06/13/2017
Update QTB logo	V1.1	05/02/2018
		_
		_
	_	_

OBLP670R-R

Disclaimer

QT-BRIGHTEK reserves the right to make changes without further notice to any products herein to improve reliability, function or design. QT-BRIGHTEK does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

Life Support Policy

QT-BRIGHTEK's products are not authorized for use as critical components in life support devices or systems without the express written approval of QT-BRIGHTEK. As used herein:

- 1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- 2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

Product: QBLP670R-R	Date: May 02, 2018	Page 9 of 9
	Version# 1.1	